Technical datasheet

Ropanyl EX 14/2 00+20 dark green M1 AS FG

Ammeraal Beltech
Innovation & Service in Belting

Article code: SBMD000035

General information	
Product group	Synthetic Belts
Industry segment	Recycling; Metal; Automotive
Main product feature	Antistatic, Abrasion resistant, Low noise, Oil & grease resistant
Indication of use	Flat, Rollers, Slider bed

Belt construction				
Number of plies		2		
Top side	material	Ropanyl, TPU		
	finish	smooth, M1 Fine matt finish		
	color	dark green		
Bottom side	material	Ropanol, PUR		
	finish	impregnated fabric		
	color	natural		

Characteristics		
Food Grade (FG)	yes	EC 1935/2004, EU 10/2011; FDA
Antistatic (AS)	yes	ISO 21178

Technical data						
Hardness	ISO 868	top side	88A	Shore		
Force at 1% elongation (static)	ISO 21181		14	N/mm	79.94	lbs/in.
Thickness	AB method KV.002	total	4.00	mm	0.16	in.
		top cover	2.00	mm	0.08	in.
Weight	AB method KV.004		4.8	kg/m²	0.98	lbs/ft²
Operating temperature	continuous	from / to	-25 / 90	°C	-13 / 194	°F
	short	from / to	-25 / 90	°C	-13 / 194	°F
Minimum pulley diameter	flexing		100	mm	3.94	in.
	backflexing		140	mm	5.51	in.
Manufacturing width	standard		3000	mm	118.11	in.
	maximum		3000	mm	118.11	in.

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive. For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the seperate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ. We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.