

Poliflex ESF 3/1 015+015 light blue M1 AS FG NL

Article code: SBPO514140

General information

Product group	Synthetic Belts
Industry segment	Agriculture:Agriculture;Tobacco
Main product feature	Antistatic, Foodgrade
Indication of use	Rollers, Flat, Troughed

Belt construction

Tension layer		polyester, flexible
Number of plies		1
Top side	material	Poliflex, PE
	finish	matt, M1 Fine matt finish
	color	Light blue
Bottom side	material	Poliflex, VLD
	finish	matt, M1 Fine matt finish
	color	Light blue

Characteristics

Food Grade (FG)	yes	According: EC 1935/2004, EU 10/2011
Anti-static (AS)	yes	

Technical data

Hardness	according to ISO 868	top side	90A Shore	
Force at 1% elongation	according to ISO 21181		3 N/mm	17.13 lbs/in.
Thickness	internal AB method KV.002	total	0.80 mm	0.03 in.
		top cover	0.15 mm	0.01 in.
Weight	internal AB method KV.004		1 kg/m ²	0.2 lbs/ft ²
Operating temperature	continuous	from/to	-20 / 50 °C	-4 / 122 °F
	short	from/to	-50 / 70 °C	-58 / 158 °F
Minimum pulley diameter	flexing		10 mm	0.39 in.
	backflexing		20 mm	0.79 in.
Belt width	standard		1500 mm	59.06 in.
	maximum		2000 mm	78.74 in.

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive.

For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the separate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F) and 50% relative humidity, unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Do not go below the initial elongation. Install the belt and tension until running perfectly under the full belt load.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.