

Ropanyl EX 10/2 0+A32 dark green AS

Article code: SBRY589731

General information

Product group	Synthetic Belts
Industry segment	Logistics
Main product feature	Antistatic
Indication of use	Flat, Rollers, Slider bed

Belt construction

Tension layer		polyester, stable
Number of plies		2
Top side	material	Ropanyl, TPU
	finish	profile, A32 Fine rib profile
	color	dark green
Bottom side	material	fabric, polyester
	finish	bare fabric
	color	natural

Characteristics

Food Grade (FG)	no	
Antistatic (AS)	yes	ISO 21178
High conductive (HC)	no	
ATEX approval	no	

Technical data

Hardness	ISO 868	top side	66A Shore		
Force at 1% elongation (static)	ISO 21181		10 N/mm	57.1 lbs/in.	
Thickness	AB method KV.002	total	2 mm	0.08 in.	
		top cover	0.7 mm	0.03 in.	
Weight	AB method KV.004		2.1 kg/m ²	0.43 lbs/ft ²	
Coefficient of friction	bottom against steel	dynamic	0.17		
		static	0.20		
	top against steel	dynamic	1.00		
		static	1.10		
Operating temperature	continuous	from / to	-20 / 90 °C	-4 / 194 °F	
	short	from / to	-30 / 110 °C	-22 / 230 °F	
Minimum pulley diameter	flexing		20 mm	0.79 in.	
	backflexing		45 mm	1.77 in.	
Manufacturing width	standard		2500 mm	98.43 in.	
	maximum		2500 mm	98.43 in.	

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive.

For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the separate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.