Technical datasheet

Ropanyl ESM 6/1 F1+02 light blue AS FG AM NF



Article code: SBRY591240

General information	
Product group	Synthetic Belts
Industry segment	Food: Meat & poultry, Confectionary & candy, Container & packaging; Fish & seafood
Main product feature	Anti-microbial, Antistatic, Foodgrade, Non-fraying
Indication of use	Slider bed, Rollers, Flat

Belt construction		
Tension layer		polyester spun, stable
Number of plies		1
Top side	material	Ropanyl, TPU
	finish	smooth, glossy
	color	Light blue
Bottom side	material	Ropanyl, TPU
	finish	profile, F1 Light fabric emboss
	color	Light blue

Characteristics		
Food Grade (FG)	yes	EC 1935/2004, EU 10/2011; FDA
Antistatic (AS)	yes	ISO 21178
High conductive (HC)	no	
ATEX approval	no	

Technical data						
Hardness	ISO 868	top side	85A	Shore		
Force at 1% elongation (static)	ISO 21181		6	N/mm	34.26	lbs/in.
Thickness	AB method KV.002	total	1.2	mm	0.05	in.
		top cover	0.2	mm	0.01	in.
Weight	AB method KV.004		1.5	kg/m²	0.31	lbs/ft²
Operating temperature	continuous	from / to	-20 / 90	°C	-4 / 194	°F
	short	from / to	-20 / 110	°C	-4 / 230	°F
Minimum pulley diameter	flexing		6	mm	0.24	in.
	backflexing		6	mm	0.24	in.
Manufacturing width	standard		2000	mm	78.74	in.
	maximum		2010	mm	79.13	in.

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive. For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the seperate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 $^{\circ}$ C (68 $^{\circ}$ F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.