

Ropanyl EM 6/2 00+02 light blue M2 AS FG AM

Article code: SBRY577981

General information

Product group	Synthetic Belts
Industry segment	Food: Confectionary & candy, Bakery; Container & packaging
Main product feature	Antistatic, Foodgrade, Anti-microbial, Knife edge transfer
Indication of use	Slider bed, Rollers, Flat

Belt construction

Tension layer		polyester, stable
Number of plies		2
Top side	material	Ropanyl, TPU
	finish	smooth, M2 Matt finish
	color	Light blue
Bottom side	material	Ropanol, PUR
	finish	impregnated fabric
	color	Light blue

Characteristics

Food Grade (FG)	yes	EC 1935/2004, EU 10/2011; FDA; Japan - MHLW No.370
Antistatic (AS)	yes	ISO 21178
High conductive (HC)	no	
ATEX approval	yes	ATEX II - KEMA 05ATEX2164 U

Technical data

Hardness	ISO 868	top side	85A Shore	
Force at 1% elongation (static)	ISO 21181		6 N/mm	34.26 lbs/in.
Thickness	AB method KV.002	total	1.5 mm	0.06 in.
		top cover	0.15 mm	0.01 in.
Weight	AB method KV.004		1.7 kg/m ²	0.35 lbs/ft ²
Heat transfer coefficient			133 W/(m ² .K)	23.44 BTU/(h.ft ² .°F)
Operating temperature	continuous	from / to	-20 / 90 °C	-4 / 194 °F
	short	from / to	-30 / 110 °C	-22 / 230 °F
Minimum pulley diameter	flexing		6 mm	0.24 in.
	backflexing		40 mm	1.57 in.
Manufacturing width	standard		2020 mm	79.53 in.
	maximum		3000 mm	118.11 in.

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive.

For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the separate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.